



Click [here](#) for the 3D model.

#### Dimensions

|    |                      |
|----|----------------------|
| L  | 5.08mm MAX           |
| H  | 6.6mm MAX            |
| T  | 3.81mm MAX           |
| S  | 5.08mm +/-0.78mm     |
| LL | 7mm MIN              |
| F  | 0.51mm +0.1/-0.025mm |

#### Packaging Specifications

|                    |           |
|--------------------|-----------|
| Packaging          | Bulk, Bag |
| Packaging Quantity | 500       |

#### General Information

|              |                              |
|--------------|------------------------------|
| Series       | GoldMax 300 Comm COG HV      |
| Style        | Radial                       |
| Description  | GoldMax, Commercial Standard |
| RoHS         | Yes                          |
| Termination  | Tin                          |
| Lead         | Wire Leads                   |
| Failure Rate | N/A                          |
| AEC-Q200     | No                           |
| Halogen Free | true                         |

#### Specifications

|  |                       |
|--|-----------------------|
| Capacitance  | 510 pF                |
| Measurement Condition  | 1MHz 1.0Vrms          |
| Capacitance Tolerance  | 5%                    |
| Voltage DC   | 500 VDC               |
| Dielectric Withstanding Voltage                                    | 750 VDC               |
| Temperature Range  | -55/+125°C            |
| Temperature Coefficient  | COG                   |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 30PPM/C, 1MHz 1.0Vrms |
| Dissipation Factor   | 0.1% 1 MHz 1.0Vrms    |
| Aging Rate   | 0% Loss/Decade Hour   |
| Insulation Resistance  | 100 GOhms             |