



Click [here](#) for the 3D model.

### Dimensions

D	136mm +2mm
L	347mm +/-2mm
L1	350mm +/-2mm
S	50mm +/-0.3mm
D1	139mm +0.5mm

### Packaging Specifications

	Through-Hole
Terminal Type	Bolt - M12x16
Packaging	Bulk, Bag
Packaging Quantity	2

### General Information

Series	C44U-M
Dielectric	Metallized Polypropylene
Style	Can
Features	DC Filtering, Energy Storage
RoHS	With Exemptions
REACH	SVHC (Pb - CAS 7439-92-1)
Lead	Screw Terminals M6
AEC-Q200	No
Typical Component Weight	5100 g
Miscellaneous	Thermal Resistance = 1.8 C/W. Weight = 12100 grams.

### Specifications

Capacitance	1400 uF
Capacitance Tolerance	10%
Voltage DC	1500 VDC
Temperature Range	-40/+85°C
Rated Temperature	75°C
Insulation Resistance	20 MOhms
Max dV/dt	13 V/us
ESR	0.78 mOhms (1kHz)
Ripple Current	100 Amps (1kHz 40C), 13000 Amps (Peak)
Inductance	80 nH