



Click [here](#) for the 3D model.

Dimensions	
L	31.5mm +0.5/-0.7mm
H	29mm +0.2/-0.7mm
T	19mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm -2mm
F	0.8mm NOM
G	0.5mm NOM

Packaging Specifications	
Packaging	Bulk, Box

General Information	
Series	C4AE
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Termination	Tin
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	20.8 g
Miscellaneous	Thermal Resistance = 29 C/W.
Notes	Not for new design – the replacement series is: C4AQ.

Specifications	
Capacitance	5 μ F
Capacitance Tolerance	5%
Voltage DC	900 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Insulation Resistance	6 GOhms
Max dV/dt	24 V/us
ESR	9.1 mOhms (10kHz 70C)
Ripple Current	7 Amps (10kHz 70C), 120 Amps (Peak)
Inductance	26 nH