



Click [here](#) for the 3D model.

Dimensions

L	31.5mm +0.5/-0.7mm
H	37mm +0.2/-0.7mm
T	22mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm -2mm
F	0.8mm NOM

Packaging Specifications

Packaging	Bulk, Box
-----------	-----------

General Information

Series	C4AE
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	31.1 g
Miscellaneous	Thermal Resistance = 23 C/W.

Specifications

Capacitance	8 uF
Capacitance Tolerance	5%
Voltage DC	900 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Insulation Resistance	3.75 GOhms
Max dV/dt	24 V/us
ESR	6.6 mOhms (10kHz 70C)
Ripple Current	9.5 Amps (10kHz 70C), 193 Amps (Peak)
Inductance	28 nH