




C4AF, Film, Metallized Polypropylene, Power, 2.5 uF, 10%, 500 VDC, 250 VAC, 85°C, 27.5 mm



General Information		
Series		C4AF
Dielectric		Metallized Polypropylene
Style		Radial
Features		Harsh Environmental Conditions
RoHS		Yes
Lead		Wire Leads
Qualification	S	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200		Yes
Typical Com	ponent Weight	16 g
Miscellaneou	IS	Rth = 36 C/W.

Click here for the 3D model.

Dimensions	
L	31.5mm +0.5/-0.7mm
Н	25mm +0.2/-0.7mm
T	13mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm +0/-2mm
F	0.8mm +/-0.05mm

Packaging Specifications		
Packaging	Bulk, Box	
Packaging Quantity	234	

Specifications		
Capacitance	2.5 uF	
Tolerance	10%	
Voltage DC	500 VDC	
Voltage AC	250 VAC	
Temperature Range	-55/+105°C	
Rated Temperature	85°C	
Insulation Resistance	12 GOhms	
Max dV/dt	30 V/us	
ESR	2.5 mOhms	
Ripple Current	5.5 Amps Irms (MAX), 75 Amps Ipkr	
Inductance	28.6 nH (ESL)	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/29/2025 © 2006 - 2025 YAGEO





C4AF, Film, Metallized Polypropylene, Power, 2.5 uF, 10%, 500 VDC, 250 VAC, 85°C, 27.5 mm

Simulations

-50.0

-60.0


S21 Phase

— S21 Magnitude

10.0 k 100.0 k 1.0 M 10.0 M 100.0 M 1.0 G

Frequency (Hz)

For the complete simulation environment please visit Y-SIM.



Generated 11/29/2025 © 2006 - 2025 YAGEO

-40.0

-60.0

-80.0

-0.4

-0.6

-0.4

-0.6

-0.8

-1.0

50.0 100.0 150.0 200.0 250.0 300.0 350.0 400.0 450.0

Voltage (VDC)



C4AF1BU4250F1XK

C4AF, Film, Metallized Polypropylene, Power, 2.5 uF, 10%, 500 VDC, 250 VAC, 85°C, 27.5 mm

These are simulations.

This is not a specification!

The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

The responses shown do not represent a specified or implied maximum capability of the device for all applications.

- The ESR used for ripple "Ripple Current/Voltage vs. Frequency" plots is the ESR at ambient temperature.

- The ESR used for ripple Ripple Currenty voltage vs. Frequency plots is the ESR at ambient temperature.
 The ESR in the "Temperature Rise vs. Ripple Current" plots is adjusted to each incremental temperature rise before the power and ripple current is calculated.
 The effects shown herein are based on measured data from a multiple part sample of the parts in question.
 Ripple capability of this device will be factored by thermal resistance (Rth) created by circuit traces (addi affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.
 The peak voltages generated in the "Temperature Rise vs. Combined Ripple Currents" plot are calculated for each frequency and are not combined with voltages
- generated at any other harmonics.

 Please consult with the catalog or field applications engineer for maximum capability of the device in specific applications.

All product information and data (collectively, the "Information") are subject to change without notice.

KEMET K-SIM is designed to simulate behavior of components with respect to frequency, ambient temperature, and DC bias levels. The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation effects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

All Information given herein is believed to be accurate and reliable, but is presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

If you have any questions please contact K-SIM.

Generated 11/29/2025 © 2006 - 2025 YAGEO