



Click [here](#) for the 3D model.

#### Dimensions

L	31.5mm +0.5/-0.7mm
H	37mm +0.2/-0.7mm
T	22mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm +0/-2mm
F	0.8mm +/-0.05mm

#### Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	64

#### General Information

Series	C4AF
Dielectric	Metallized Polypropylene
Style	Radial
Features	Harsh Environmental Conditions
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	38 g
Miscellaneous	Rth = 23 C/W.

#### Specifications

Capacitance	1.8 uF
Capacitance Tolerance	10%
Voltage DC	1000 VDC
Voltage AC	500 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Insulation Resistance	16.67 GOhms
Max dV/dt	70 V/us
ESR	1.8 mOhms
Ripple Current	6.7 Amps Irms (MAX), 126 Amps Ipk
Inductance	36.4 nH (ESL)