




C44U, Film, Metallized Polypropylene, DC Link, 500 uF, 10%, 1,100 VDC, 317 mm



Click here for the 3D model.

Dimensions	
D	85mm +1mm
L	174mm +0.5mm
L1	180mm +/-1mm
S	31.7mm +/-0.2mm

Packaging Specifications		
Terminal Type	Bolt - M12x16	
Packaging	Bulk, Bag	
Packaging Quantity	5	

General Information	
Series	C44U
Dielectric	Metallized Polypropylene
Style	Can
Features	Standard Duty
RoHS	With Exemptions
REACH	SVHC (Pb - CAS 7439-92-1)
SCIP Number	cc1c1ec4-db9e-4815-b26b-e8a 34ddfb776
Lead	Threaded Studs M8
AEC-Q200	No
Typical Component Weight	1,280 g
Miscellaneous	Thermal Resistance = 3.4 C/W. Weight = 1120 grams.

Specifications	
Capacitance	500 uF
Tolerance	10%
Voltage DC	1100 VDC
Temperature Range	-40/+85°C
Rated Temperature	75°C
Insulation Resistance	60 MOhms
Max dV/dt	12 V/us
ESR	1.1 mOhms (10kHz)
Ripple Current	90 Amps (10kHz 40C), 6000 Amps (Peak)
Inductance	80 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/23/2025 © 2006 - 2025 YAGEO