



Click [here](#) for the 3D model.

Dimensions

D	116mm +2mm
L	273mm +/-2mm
L1	276mm +/-2mm
S	50mm +/-0.3mm
D1	119mm +0.5mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	4

General Information

Series	C44U-T
Dielectric	Metallized Polypropylene
Style	Can
Features	DC Filtering, Energy Storage
RoHS	With Exemptions
Lead	Screw Terminals M6
AEC-Q200	No
Typical Component Weight	3270 g
Miscellaneous	Thermal Resistance = 1.8C/W.

Specifications

Capacitance	700 uF
Capacitance Tolerance	10%
Voltage DC	1500 VDC
Temperature Range	-40/+105°C
Rated Temperature	85°C
Insulation Resistance	1.9 GOhms
Max dV/dt	10 V/us
ESR	1.9 mOhms
Ripple Current	93 Amps (10kHz 55C), 7155 Amps (Peak)
Inductance	80 nH