




C4AQ-P, Film, Metallized Polypropylene, Automotive DC Link, 4 uF, 5%, 700 VDC, 27.5 mm



General Information	
Series	C4AQ-P
Dielectric	Metallized Polypropylene
Style	Radial
Features	DC Filtering
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	15.7 g
Miscellaneous	Rth = 36 C/W.

Click here for the 3D model.

Dimensions	
L	31.5mm +0.5/-0.7mm
Н	25mm +0.2/-0.7mm
T	13mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm -2mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Box
Packaging Quantity	234

Specifications	
Capacitance	4 uF
Tolerance	5%
Voltage DC	700 VDC
Temperature Range	-55/+125°C
Insulation Resistance	7.5 GOhms
Max dV/dt	65 V/us
ESR	14.19 mOhms (10kHz 70C)
Ripple Current	7.5 Amps Irms (10kHz 75C), 260 Amps Ipkr
Inductance	22 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/21/2025 © 2006 - 2025 YAGEO