

## C4AQSBW4600A3FJ

C4AQ, Film, Metallized Polypropylene, Automotive DC Link, 6 uF, 5%, 1,500 VDC, 70°C, 37.5 mm



Click [here](#) for the 3D model.

### General Information

Series	C4AQ
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	4 Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	41.2 g
Miscellaneous	Rth = 20 C/W.

### Specifications

Capacitance	6 uF
Tolerance	5%
Voltage DC	1500 VDC
Temperature Range	-55/+105°C
Rated Temperature	70°C
Insulation Resistance	5 GOhms
Max dV/dt	22 V/us
ESR	9.4 mOhms (10kHz 70C)
Ripple Current	11.8 Amps Irms (10kHz 70C), 132 Amps Ipk
Inductance	12 nH

### Dimensions

L	42mm +0.6/-0.7mm
H	40mm +0.2/-0.7mm
T	20mm +0.4/-0.7mm
S	37.5mm +/-0.4mm
S1	10.2mm +/-0.4mm
LL	6mm +0/-2mm
F	1.2mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	58

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.