




C4AF, Film, Metallized Polypropylene, Power, 6.8 uF, 10%, 1,000 VDC, 500 VAC, 85°C, 37.5 mm



Click here for the	he 3D model.
--------------------	--------------

General Information	
Series	C4AF
Dielectric	Metallized Polypropylene
Style	Radial
Features	Harsh Environmental Conditions
RoHS	Yes
Lead	4 Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	103 g
Miscellaneous	Rth = 13 C/W.

Dimensions	
L	42mm +0.6/-0.7mm
Н	50mm +0.2/-0.7mm
Т	35mm +0.4/-0.7mm
S	37.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm +0/-2mm
F	1.2mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Box
Packaging Quantity	30

Specifications	
Capacitance	6.8 uF
Tolerance	10%
Voltage DC	1000 VDC
Voltage AC	500 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Insulation Resistance	4.41 GOhms
Max dV/dt	35 V/us
ESR	6.8 mOhms
Ripple Current	14.7 Amps Irms (MAX), 238 Amps Ipkr
Inductance	18.2 nH (ESL)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/02/2025 © 2006 - 2025 YAGEO