



Click [here](#) for the 3D model.

#### Dimensions

L	31.5mm +0.5/-0.7mm
H	29mm +0.2/-0.7mm
T	19mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm +0/-2mm
F	0.8mm +/-0.05mm

#### Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	72

#### General Information

Series	C4AQ
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	21.8 g
Miscellaneous	Rth = 29 C/W.

#### Specifications

Capacitance	3.3 uF
Capacitance Tolerance	5%
Voltage DC	1300 VDC
Temperature Range	-55/+105°C
Rated Temperature	70°C
Insulation Resistance	9.09 GOhms
Max dV/dt	29 V/us
ESR	11.2 mOhms (10kHz 70C)
Ripple Current	9.1 Amps Irms (10kHz 70C), 95 Amps Ipk
Inductance	25 nH