



Click [here](#) for the 3D model.

Dimensions

L	42mm +0.6/-0.7mm
H	37mm +0.2/-0.7mm
T	28mm +0.4/-0.7mm
S	37.5mm +/-0.4mm
S1	10.2mm +/-0.4mm
LL	6mm +0/-2mm
F	1.2mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	36

General Information

Series	C4AQ
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	4 Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	54.7 g
Miscellaneous	Rth = 18 C/W.

Specifications

Capacitance	10 uF
Capacitance Tolerance	5%
Voltage DC	1300 VDC
Temperature Range	-55/+105°C
Rated Temperature	70°C
Insulation Resistance	3 GOhms
Max dV/dt	20 V/us
ESR	6.3 mOhms (10kHz 70C)
Ripple Current	15 Amps Irms (10kHz 70C), 196 Amps Ipk
Inductance	10 nH