

## C4ATHBW4900A3LJ

C4AT, Film, Metallized Polypropylene, Power, 9 uF, 5%, 600 VDC, 350 VAC, 70°C, 37.5 mm



Click [here](#) for the 3D model.

### General Information

Series	C4AT
Dielectric	Metallized Polypropylene
Style	Radial
Features	Switching
RoHS	Yes
Lead	4 Wire Leads
AEC-Q200	No
Typical Component Weight	72.5 g

### Dimensions

L	42mm -0.7mm
H	45mm -0.7mm
T	30mm -0.7mm
S	37.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm -2mm
F	1.2mm NOM

### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	36

### Specifications

Capacitance	9 uF
Tolerance	5%
Voltage DC	600 VDC
Voltage AC	350 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Dissipation Factor	0.05%
Max dV/dt	70 V/us
ESR	1.9 mOhms (100kHz)
Ripple Current	29 Amps (100kHz 70C), 632 Amps (Peak)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.