



Click [here](#) for the 3D model.

#### Dimensions

L	41.5mm +1.5/-0.7mm
H	40mm +0.2/-0.7mm
T	20mm +0.4/-0.7mm
S	25.5mm +/-0.2mm
S1	21.5mm +/-0.2mm
S2	29.5mm +/-0.2mm
P	10.5mm NOM

#### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	52

#### General Information

Series	C4BS
Dielectric	Metallized Polypropylene
Style	Radial
Features	IGBT Circuit
RoHS	Yes
Lead	Flat Tabs
AEC-Q200	No
Typical Component Weight	61.54 g
Miscellaneous	KEMET Style A Tabs.

#### Specifications

Capacitance	0.1 uF
Capacitance Tolerance	5%
Voltage DC	3000 VDC
Voltage AC	750 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Max dV/dt	2068 V/us
ESR	17.3 mOhms (100kHz)
Ripple Current	12 Amps (100kHz 70C), 207 Amps (Peak)
Inductance	41 nH