



FRONT VIEW

SIDE VIEW

 Click [here](#) for the 3D model.

General Information

Series	C4C
Dielectric	Metallized Polypropylene
Style	Axial
RoHS	Yes
Lead	Wire Leads
Typical Component Weight	16 g
Miscellaneous	Polyester Tape & Resin Protection.

Dimensions

D	22.5mm NOM
L	44mm NOM
LL	40mm +/-5mm
F	1mm NOM

Specifications

Capacitance	0.068 uF
Tolerance	5%
Voltage DC	3000 VDC
Voltage AC	750 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Dissipation Factor	0.05%
Max dV/dt	1,250 V/us
ESR	18.3 mOhms (100kHz)
Ripple Current	9 Amps (100kHz 70C), 85 Amps (Peak)

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	70

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.