



### FRONT VIEW



### SIDE VIEW



Click [here](#) for the 3D model.

#### Dimensions

D	34.5mm MAX
L	58mm MAX
LL	40mm +/-5mm
F	1.2mm NOM

#### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	30

#### General Information

Series	C4G
Dielectric	Metallized Polypropylene
Style	Axial
Features	Switching
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	44.8 g
Miscellaneous	Polyester Tape & Resin Protection.

#### Specifications

Capacitance	10 uF
Capacitance Tolerance	5%
Voltage DC	600 VDC
Voltage AC	330 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Dissipation Factor	0.05%
Max dV/dt	30 V/us
ESR	5.3 mOhms (100kHz)
Ripple Current	12 Amps (100kHz 70C), 300 Amps (Peak)