



The measurement position of Lead Spacing (S) and Width (V) is critical in straight lead capacitors.

Click [here](#) for the 3D model.

Dimensions

| | |
|----|-----------------|
| D | 7mm MAX |
| T | 5mm MAX |
| S | 10mm +/-1mm |
| H0 | 18mm +2/-0mm |
| F | 0.55mm +/-0.1mm |

Packaging Specifications

| | |
|--------------------|------|
| Packaging | Ammo |
| Packaging Quantity | 1000 |

General Information

| | |
|--------------------------|---------------------------|
| Series | C900AC SFTY X1-440 Y2-300 |
| Style | Radial Disc |
| RoHS | Yes |
| Termination | Tin |
| Failure Rate | N/A |
| Qualifications | VDE, ENEC, UL, cUL |
| AEC-Q200 | No |
| Halogen Free | Yes |
| Typical Component Weight | 500 mg |

Specifications

| | |
|---------------------------------|----------------------------|
| Capacitance | 1000 pF |
| Capacitance Tolerance | 20% |
| Voltage AC | 440 VAC (X1), 300 VAC (Y2) |
| Dielectric Withstanding Voltage | 2600 VDC |
| Temperature Range | -40/+125°C |
| Temperature Coefficient | Y5U |
| Dissipation Factor | 2.5% |
| Insulation Resistance | 10 GOhms |
| Safety Class | X1/Y2 |