



Click [here](#) for the 3D model.

#### Dimensions

L	57.5mm +1.2/-0.7mm
H	50mm +0.3/-0.7mm
T	35mm +0.5/-0.7mm
S	41mm +/-0.2mm
S1	37mm +/-0.2mm
S2	45mm +/-0.2mm
P	25mm NOM

#### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	21

#### General Information

Series	C4BS
Dielectric	Metallized Polypropylene
Style	Radial
Features	IGBT Circuit
RoHS	Yes
Lead	Flat Tabs
AEC-Q200	No
Typical Component Weight	131.4 g
Miscellaneous	KEMET Style A Tabs.

#### Specifications

Capacitance	5 uF
Capacitance Tolerance	5%
Voltage DC	850 VDC
Voltage AC	550 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Max dV/dt	469 V/us
ESR	1.9 mOhms (100kHz)
Ripple Current	42 Amps (100kHz 70C), 2347 Amps (Peak)
Inductance	48 nH