



Click [here](#) for the 3D model.

Dimensions

L	42.5mm +1.5/-0.7mm
H	37mm +0.2/-0.7mm
T	28mm +0.4/-0.7mm
S	22mm +/-0.2mm
S1	16mm +/-0.2mm
S2	28mm +/-0.2mm
P	6mm NOM

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	36

General Information

Series	C4BS
Dielectric	Metallized Polypropylene
Style	Radial
Features	IGBT Circuit
RoHS	Yes
Lead	Flat Tabs
AEC-Q200	No
Typical Component Weight	61.94 g
Miscellaneous	KEMET Style F Tabs.

Specifications

Capacitance	1.5 uF
Capacitance Tolerance	5%
Voltage DC	1000 VDC
Voltage AC	600 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Max dV/dt	827 V/us
ESR	2.5 mOhms (100kHz)
Ripple Current	30 Amps (100kHz 70C), 1241 Amps (Peak)
Inductance	36 nH