



### FRONT VIEW



### SIDE VIEW



Click [here](#) for the 3D model.

### Dimensions

D	17mm NOM
L	33mm NOM
LL	40mm +/-5mm
F	1mm NOM

### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	150

### General Information

Series	C4C
Dielectric	Metallized Polypropylene
Style	Axial
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	6.9 g
Miscellaneous	Polyester Tape & Resin Protection.

### Specifications

Capacitance	0.022 uF
Capacitance Tolerance	5%
Voltage DC	3000 VDC
Voltage AC	750 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Dissipation Factor	0.05%
Max dV/dt	2100 V/us
ESR	41.6 mOhms (100kHz)
Ripple Current	5 Amps (100kHz 70C), 46 Amps (Peak)