



Click [here](#) for the 3D model.

Dimensions

D	90mm NOM
L	61mm NOM

Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------

General Information

Series	C4DR
Dielectric	Metallized Polypropylene
Style	Door Knob
Features	GTO
RoHS	With Exemptions
REACH	SVHC (Pb - CAS 7439-92-1)
Lead	Screw Terminals M8
AEC-Q200	No
Miscellaneous	Thermal Resistance = 1.5 C/W. Peak Voltage = 560 VDC. Surge Voltage = 600 VDC.

Specifications

Capacitance	110 uF
Capacitance Tolerance	5%
Voltage AC	160 VAC
Voltage DC	400 VDC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Max dV/dt	25 V/us
ESR	1.5 mOhms (100kHz)
Ripple Current	70 Amps (100kHz 70C), 2560 Amps (Peak)