



Click [here](#) for the 3D model.

Dimensions

D	50mm +1mm
L	133mm +/-2mm

Packaging Specifications

Mounting	Bolt - M12x12.5
Packaging	Bulk, Bag
Packaging Quantity	40

General Information

Series	C87
Dielectric	Film/Foil Polypropylene
Style	Can
Description	Aluminum Case, Plastic Cover, Spun Seal
Features	Spun Seal, Safety Class S2, UL_94 V0 Disk
RoHS	Yes
Lead	Fast On (2+2)
Qualifications	UL, VDE, CQC, CSA (240VAC), UL_94 V0 Disk
AEC-Q200	No
Typical Component Weight	274 g

Specifications

Capacitance	50 uF
Capacitance Tolerance	5%
Voltage AC	470 VAC
Temperature Range	-25/+85°C
Rated Temperature	85°C
Max dV/dt	20 V/us