


C901U500JZSDBAWL35

Obsolete

C900AC SFTY X1-440 Y2-300, Ceramic, 50 pF, 5%, 440 VAC (X1), 300 VAC (Y2), SL, 10 mm



| General Information | |
|---------------------|---------------------------|
| Series | C900AC SFTY X1-440 Y2-300 |
| Style | Radial Disc |
| RoHS | Yes |
| Termination | Tin |
| Lead | V-Crimp |
| Failure Rate | N/A |
| Qualifications | VDE, ENEC, UL, cUL |
| AEC-Q200 | No |

Click here for the 3D model.

| Dimensions | |
|------------|-----------------|
| D | 7mm MAX |
| Т | 5mm MAX |
| S | 10mm +/-1mm |
| LL | 3.5mm +/-1mm |
| F | 0.55mm +/-0.1mm |

| Packaging Specifications | |
|--------------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 500 |

| Specifications | |
|-----------------------|----------------------------|
| Capacitance | 50 pF |
| Tolerance | 5% |
| Voltage AC | 440 VAC (X1), 300 VAC (Y2) |
| Temperature Range | -40/+125°C |
| Temp. Coefficient | SL |
| Insulation Resistance | 10 GOhms |
| Safety Class | X1/Y2 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/26/2025 © 2006 - 2025 YAGEO