



The measurement position of Lead Spacing (S) and Width (V) is critical in straight lead capacitors.

General Information

Series	C900AC SFTY X1-400 Y2-250
Style	Radial Disc
RoHS	Yes
Termination	Tin
Failure Rate	N/A
Qualifications	VDE, ENEC, UL, cUL
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	1.6 g

Specifications

Capacitance	0.01 uF
Capacitance Tolerance	20%
Voltage AC	400 VAC (X1), 250 VAC (Y2)
Dielectric Withstanding Voltage	2600 VDC
Temperature Range	-40/+125°C
Temperature Coefficient	Y5V
Dissipation Factor	5%
Insulation Resistance	10 GOhms
Safety Class	X1/Y2

Click [here](#) for the 3D model.

Dimensions

D	15mm MAX
T	5mm MAX
S	10mm +/-1mm
LL	4.5mm +/-1mm
F	0.55mm +/-0.1mm
G	3mm MAX

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	500