



Click [here](#) for the 3D model.

#### General Information

|             |  |
|-------------|--|
| Series      | Array Comm X7R Flex                          |
| Style       | SMD Array                                    |
| Description | SMD, MLCC, Array, Flex Termination, Class II |
| RoHS        | Yes  |
| Termination | Flexible Termination                         |
| AEC-Q200    | No   |
| Chip Size   | 0612   |
| MSL         | 1  |

#### Dimensions

|   |                 |
|---|-----------------|
| L | 1.6mm +/-0.2mm  |
| W | 3.2mm +/-0.2mm  |
| T | 0.8mm +/-0.10mm |
| P | 0.8mm +/-0.10mm |

#### Packaging Specifications

|                    |                        |
|--------------------|------------------------|
| Packaging          | T&R, 180mm, Paper Tape |
| Packaging Quantity | 4000                   |

#### Specifications

|                       |                  |
|-----------------------|------------------|
| Capacitance           | 390 pF           |
| Tolerance             | 5%               |
| Voltage DC            | 10 VDC           |
| Temperature Range     | -55/+125°C       |
| Temp. Coefficient     | X7R              |
| Dissipation Factor    | 5% 1 kHz 1.0Vrms |
| Insulation Resistance | 100 GOhms        |