



Click [here](#) for the 3D model.

**General Information**

Series	Array Comm X7R Flex
Style	SMD Array
Description	SMD, MLCC, Array, Flex Termination, Class II
RoHS	Yes
Termination	Flexible Termination
AEC-Q200	No
Chip Size	0612
MSL	1

**Dimensions**

L	1.6mm +/-0.2mm
W	3.2mm +/-0.2mm
T	0.8mm +/-0.10mm

**Packaging Specifications**

Packaging	T&R, 180mm, Paper Tape
Packaging Quantity	4000

**Specifications**

Capacitance	0.039 uF
Capacitance Tolerance	5%
Voltage DC	16 VDC
Temperature Range	-55/+125°C
Temperature Coefficient	X7R
Dissipation Factor	3.5% 1 kHz 1.0Vrms
Insulation Resistance	25.641 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.