

CBR06C100JAGAC

CBR-SMD RF COG, Ceramic, 10 pF, 5%, 250 VDC, COG, SMD, Fixed, RF, Ultra High Q, Low ESR, Class I, 0603



Click [here](#) for the 3D model.

Dimensions

| | |
|-----------|-----------------|
| Chip Size | 0603 |
| L | 1.6mm +/-0.1mm |
| W | 0.8mm +/-0.1mm |
| T | 0.8mm +/-0.07mm |
| B | 0.4mm +/-0.15mm |

Packaging Specifications

| | |
|--------------------|--------------------------|
| Packaging | T&R, 180mm, Plastic Tape |
| Packaging Quantity | 4000 |

General Information

| | |
|--------------------------|--|
| Series | CBR-SMD RF COG |
| Style | SMD Chip |
| Description | SMD, Fixed, RF, Ultra High Q, Low ESR, Class I |
| Features | Ultra High Q, Low ESR, Class I |
| RoHS | Yes |
| Termination | Tin |
| Marking | No |
| AEC-Q200 | No |
| Typical Component Weight | 5.29 mg |
| Notes | Solder Wave or Solder Reflow. |
| Shelf Life | 78 Weeks |
| MSL | 1 |

Specifications

| | |
|---------------------------------|---------------------|
| Capacitance | 10 pF |
| Capacitance Tolerance | 5% |
| Voltage DC | 250 VDC |
| Dielectric Withstanding Voltage | 500 VDC |
| Temperature Range | -55/+125°C |
| Temperature Coefficient | COG |
| Dissipation Factor | 0.167% |
| Aging Rate | 0% Loss/Decade Hour |
| Insulation Resistance | 10 GOhms |
| Quality Factor | 600 |