



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|------------------------------------------------|
| Series | CBR-SMD RF COG |
| Style | SMD Chip |
| Description | SMD, Fixed, RF, Ultra High Q, Low ESR, Class I |
| Features | Ultra High Q, Low ESR, Class I |
| RoHS | Yes |
| Termination | Tin |
| Marking | false |
| AEC-Q200 | No |
| Typical Component Weight | 12.03 mg |
| Notes | Solder Wave or Solder Reflow. |
| Shelf Life | 78 Weeks |
| MSL | 1 |

Specifications

| | |
|---------------------------------|---------------------|
| Capacitance | 3.3 pF |
| Capacitance Tolerance | +/-0.1 pF |
| Voltage DC | 500 VDC |
| Dielectric Withstanding Voltage | 750 VDC |
| Temperature Range | -55/+125°C |
| Temperature Coefficient | COG |
| Dissipation Factor | 0.215% |
| Aging Rate | 0% Loss/Decade Hour |
| Insulation Resistance | 10 GOhms |
| Quality Factor | 466 |

Dimensions

| | |
|-----------|-----------------|
| Chip Size | 0805 |
| L | 2mm +/-0.2mm |
| W | 1.25mm +/-0.2mm |
| T | 0.85mm +/-0.1mm |
| B | 0.5mm +/-0.2mm |

Packaging Specifications

| | |
|--------------------|--------------------------|
| Packaging | T&R, 180mm, Plastic Tape |
| Packaging Quantity | 4000 |