



Click [here](#) for the 3D model.

#### Dimensions

|           |                |
|-----------|----------------|
| Chip Size | 0603           |
| L         | 1.6mm +/-0.1mm |
| W         | 0.8mm +/-0.1mm |
| T         | 0.8mm +/-0.1mm |
| B         | 0.4mm +/-0.2mm |

#### Packaging Specifications

|                    |                          |
|--------------------|--------------------------|
| Packaging          | T&R, 180mm, Plastic Tape |
| Packaging Quantity | 4000                     |

#### General Information

|                          |  |
|--------------------------|--|
| Series                   | CBR-SMD RF Auto COG                            |
| Style                    | SMD Chip                                       |
| Description              | SMD, Fixed, RF, Ultra High Q, Low ESR, Class I |
| Features                 | Ultra High Q, Low ESR, Class I                 |
| RoHS                     | Yes  |
| Termination              | Tin  |
| Marking                  | false  |
| Qualifications           | AEC-Q200                                       |
| AEC-Q200                 | Yes  |
| Halogen Free             | true   |
| Typical Component Weight | 5.29 mg  |
| Notes                    | Solder Wave or Solder Reflow.                  |
| Shelf Life               | 78 Weeks                                       |
| MSL                      | 1  |

#### Specifications

|  |                           |
|--|---------------------------|
| Capacitance  | 8.2 pF                    |
| Capacitance Tolerance  | +/-0.25 pF                |
| Voltage DC   | 50 VDC                    |
| Dielectric Withstanding Voltage                                    | 125 VDC                   |
| Temperature Range  | -55/+125°C                |
| Temperature Coefficient  | COG                       |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 30 ppm/C, 1MHz<br>1.0Vrms |
| Dissipation Factor   | 0.18% 1MHz<br>1.0Vrms     |
| Aging Rate   | 0% Loss/Decade<br>Hour    |
| Insulation Resistance  | 10 GOhms                  |
| Quality Factor   | 564                       |