



Click [here](#) for the 3D model.

**General Information**

Series	CGP DISC Comm HV
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	Wire Leads
Failure Rate	N/A
AEC-Q200	No
Halogen Free	true

**Dimensions**

D	25.5mm MAX
T	10mm MAX
S	10mm NOM
LL	25mm MIN
F	0.6mm +/-0.1mm
V	4.9mm +/-0.5mm

**Specifications**

Capacitance	6800 pF
Capacitance Tolerance	20%
Voltage DC	10000 VDC
Temperature Range	-30/+85°C
Temperature Coefficient	Y5U

**Packaging Specifications**

Packaging	Bulk
Packaging Quantity	200

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.