



Click [here](#) for the 3D model.

General Information

Series	EDH
Dielectric	Aluminum Electrolytic
Style	SMD Can
Description	Surface Mount, Aluminum Electrolytic
RoHS	Yes
Lead	V-Chip
AEC-Q200	No

Specifications

Capacitance	2200 uF
Capacitance Tolerance	20%
Voltage DC	25 VDC, 32 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	2000 Hrs
Dissipation Factor	26% 120Hz 20C
Ripple Current	900 mAmps (120Hz 105C)
Compare Ripple Current at 120Hz	0.9
Leakage Current	550 uA (2min 20°C)
Impedance Ratio at -25C	2
Impedance Ratio at -40C	4
High Temperature Solder	true

Dimensions

D	16mm +/-0.5mm
L	16.5mm +/-0.5mm
W	2mm +/-0.2mm
F	0.3mm MAX
A	16.3mm +/-0.2mm
B	16.3mm +/-0.2mm
C	18.7mm MAX
E	5.8mm +/-0.2mm
G	1mm +/-0.2mm
P	6mm +/-0.2mm

Packaging Specifications

Packaging

T&R