



Click [here](#) for the 3D model.

### Dimensions

|    |                 |
|----|-----------------|
| L  | 15mm MAX        |
| W  | 7.5mm MAX       |
| H  | 10mm MAX        |
| LL | 1mm +/-0.2mm    |
| S  | 5.08mm +/-0.2mm |
| S1 | 2.54mm +/-0.2mm |
| F  | 1mm +/-0.2mm    |
| F1 | 2mm +/-0.1mm    |

### Packaging Specifications

|           |     |
|-----------|-----|
| Packaging | T&R |
|-----------|-----|

### General Information

|             |   |
|-------------|---|
| Series      | EE2   |
| Style       | SMD   |
| Description | Miniature Signal Relay, Double Coil Latch   |
| Features    | Compact and light weight. FCC (1500 V) and Telcordia (2500 V) surge capacity. UL recognized and CSA certified. Low power consumption (100-200 mW). ND type (High insulation). NKX type (High breakdown voltage) can withstand 1.5KVAC at open contacts. |
| RoHS        | Yes   |
| Coil Type   | Double Coil (Latching)  |

### Specifications

|                         |                                      |
|-------------------------|--------------------------------------|
| Temperature Range       | -40/+85°C                            |
| Coil Voltage            | 12 V                                 |
| Coil Resistance         | 1028 Ohms +/-10%                     |
| Contact Form            | 2 Form C (DPDT)                      |
| Contact Material        | Silver alloy with gold alloy overlay |
| Voltage Characteristics | 9 (Set/Reset)                        |
| Switching Power         | 60 W, 125 VA                         |
| Switching Voltage DC    | 220 V                                |
| Switching Voltage AC    | 250 VAC                              |
| Switching Current       | 2 A                                  |
| Contact Current Class   | >10A                                 |
| Carrying Current        | 2 Amps                               |
| Contact Resistance      | 75 mOhms                             |
| Operation Time          | Approximately 2ms                    |
| Release Time            | Approximately 1ms                    |
| Insulation Resistance   | 1 GOhms                              |
| Withstanding Voltage    | 1000 VAC (1min) 1500 V Surge         |