



Click [here](#) for the 3D model.

#### General Information

Series	ELG
Dielectric	Aluminum Electrolytic
Style	Snap-In
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No

#### Dimensions

D	25mm +1mm
L	50mm +2mm
S	10mm +/-0.5mm
LL	4mm +/-1mm
F	1.5mm +/-0.1mm

#### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	200

#### Specifications

Capacitance	6800 uF
Capacitance Tolerance	20%
Voltage DC	50 VDC, 63 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	2000 Hrs
Dissipation Factor	30% 120Hz 20C
ESR	0.059 Ohms (120Hz 20C)
Ripple Current	3.3 Amps (120Hz 105C)
Leakage Current	3 mA (5min 20°C)
Impedance Ratio at -25C	2
Impedance Ratio at -40C	6