


ESD-R-19M-H

Aliases (UECESDR19MH000)

EMI Suppression, KEMET, ESD-R-H, Round - Toroidal, Noise Suppression



	3D model.	Case Color
Click here for the 3D model.		Toroidal
		Materials
		Core
Dimensions		Specifications
D 22mm MAX		Temperature Range
D2 7.7mm +/-1.0	mm	Effective Frequency

Packaging Specifications			
Packaging	Tray, Box		
Packaging Quantity	480		
Typical Component Weight	11.8 g		

14mm MAX

Т

General Information				
Series	ESD-R-H			
Style	Round - Toroidal			
Cable Type	Round Cable			
Description	EMI Core Solid, For Round Cables, Toroidal Cores			
Features	High Heat Resistance, Cable Holding Mechanism			
RoHS	Yes			
Qualifications	UL94V-0			
AEC-Q200	No			
Case Color	White			
Toroidal	ESD-R-19S			
Materials	Mn-Zn			
Core	Mn-Zn Ferrite			

Specifications	
Temperature Range	-40/+120°C
Effective Frequency	10 MHz (AM Band Range)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/06/2025 © 2006 - 2025 YAGEO