


[Click here](#) for the 3D model.

General Information

Series	EDH
Dielectric	Aluminum Electrolytic
Style	SMD Can
Description	Surface Mount, Aluminum Electrolytic
RoHS	Yes
Lead	V-Chip

Dimensions

D	6.3mm +/-0.5mm	Capacitance	100 uF
L	7.7mm +/-0.3mm	Tolerance	20%
W	0.65mm +/-0.1mm	Voltage DC	25 VDC, 32 VDC (Surge)
F	0.3mm MAX	Temperature Range	-40/+105°C
A	6.6mm +/-0.2mm	Rated Temperature	105°C
B	6.6mm +/-0.2mm	Life	2000 Hrs
C	7.8mm MAX	Dissipation Factor	16% 120Hz 20C
E	2.4mm +/-0.2mm	Ripple Current	100 mAmps (120Hz 105C)
G	0.35mm +0.15/-0.2mm	Compare Ripple Current at 120Hz	0.1
P	2.1mm +/-0.2mm	High Temperature Solder	Yes

Packaging Specifications

Packaging	T&R	Leakage Current	25 uA (2min 20°C)
		Impedance Ratio at -25C	2

Impedance Ratio at -40C 4

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.