



Click [here](#) for the 3D model.

General Information

Series	EDH
Dielectric	Aluminum Electrolytic
Style	SMD Can
Description	Surface Mount, Aluminum Electrolytic
RoHS	Yes
Lead	V-Chip
AEC-Q200	No

Specifications

Capacitance	470 uF
Capacitance Tolerance	20%
Voltage DC	35 VDC, 44 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	2000 Hrs
Dissipation Factor	22% 120Hz 20C
Ripple Current	520 mAmps (120Hz 105C)
Compare Ripple Current at 120Hz	0.52
Leakage Current	164.5 uA (2min 20°C)
Impedance Ratio at -25C	2
Impedance Ratio at -40C	3
High Temperature Solder	true

Dimensions

D	12.5mm +/-0.5mm
L	13.5mm +/-0.5mm
W	1.25mm +/-0.2mm
F	0.3mm MAX
A	12.8mm +/-0.2mm
B	12.8mm +/-0.2mm
C	15.2mm MAX
E	4.9mm +/-0.2mm
G	1mm +/-0.2mm
P	4.6mm +/-0.2mm

Packaging Specifications

Packaging

T&R