


TERMINAL END VIEW



Click [here](#) for the 3D model.

General Information

| | |
|-------------|-------------------------------------|
| Series | ESL |
| Dielectric | Aluminum Electrolytic |
| Style | Radial |
| Description | Single Ended, Aluminum Electrolytic |
| RoHS | Yes |
| Lead | Wire Leads |
| AEC-Q200 | No |

Dimensions

| | |
|-------------|--------------|
| D | 5mm +/-0.5mm |
| L | 11mm +1.5mm |
| S | 2mm +/-0.5mm |
| LL Negative | 15mm MIN |
| LL Positive | 20mm MIN |
| F | 0.5mm NOM |

Specifications

| | |
|-------------------------|-------------------------|
| Capacitance | 100 uF |
| Capacitance Tolerance | 20% |
| Voltage DC | 16 VDC, 20 VDC (Surge) |
| Temperature Range | -40/+105°C |
| Rated Temperature | 105°C |
| Life | 8000 Hrs |
| Dissipation Factor | 16% |
| ESR | 0.23 Ohms (100kHz 20C) |
| Ripple Current | 345 mAmps (100kHz 105C) |
| Leakage Current | 16 uA (2min 20°C) |
| Impedance Ratio at -40C | 8 |

Packaging Specifications

| | |
|-----------|-----------|
| Packaging | Bulk, Bag |
|-----------|-----------|

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.