



Note: '()' correspond to the letters used in the product bulletin

Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|-----------------------|
| Series | SPC/F127 |
| Dielectric | Double Metallized PPS |
| Style | SMD Chip |
| RoHS | Yes |
| AEC-Q200 | No |
| Typical Component Weight | 2.02 g |
| Shelf Life | 104 Weeks |
| MSL | 2 |

Dimensions

| | |
|-----------|-----------------|
| Chip Size | 6560 |
| L | 16.5mm +/-0.2mm |
| W | 15mm +/-0.2mm |
| T | 7mm +/-0.2mm |
| F | 0.5mm NOM |

Packaging Specifications

| | |
|--------------------|-----|
| Packaging | T&R |
| Packaging Quantity | 500 |

Specifications

| | |
|-----------------------|-------------------------------------|
| Capacitance | 0.047 uF |
| Tolerance | 10% |
| Voltage DC | 630 VDC |
| Voltage AC | 350 VAC |
| Temperature Range | -55/+125°C |
| Rated Temperature | 100°C |
| Dissipation Factor | 0.1% 1kHz, 0.15% 10kHz, 0.2% 100kHz |
| Insulation Resistance | 100 GOhms |
| Max dV/dt | 550 V/us |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.