




F161, Film, Metallized Polyester Stacked, Automotive Grade, 0.1 uF, 10%, 630 VDC, 250 VAC, 85°C, 7 mm, 6560 / 165152



Note: '()' correspond to the letters used in the product bulletin

Packaging Quantity

Click here for the 3D model.

Dimensions	
L	16.5mm +/-0.2mm
W	15mm +/-0.2mm
Т	7mm +/-0.2mm
F	0.5mm NOM
Case Code (EIA / mm)	6560 / 165152
Packaging Specifications	
Packaging	T&R

500

General Information	
Series	F161
Dielectric	Metallized Polyester Stacked
Style	SMD Chip
Features	Automotive Grade
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	3.86 g
Miscellaneous	Add.
Shelf Life	104 Weeks
MSL	3

Specifications	
Capacitance	0.1 uF
Tolerance	10%
Voltage DC	630 VDC
Voltage AC	250 VAC
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	0.8% 1kHz, 1.2% 10kHz, 2.5% 100kHz
Insulation Resistance	1GOhms
Max dV/dt	250 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/12/2025 © 2006 - 2025 YAGEO