


GPC16.5683K1000C31TR24

Aliases (F117ZS683K1K0V)

Obsolete

GPC/F117, Film, Double Metallized PEN, General Purpose, 0.068 uF, 10%, 1,000 VDC, 350 VAC, 100°C, 6560, 7 mm



General Information	
Series	GPC/F117
Dielectric	Double Metallized PEN
Style	SMD Chip
RoHS	Yes
AEC-Q200	No
Typical Component Weight	2.02 g
Shelf Life	104 Weeks
MSL	3

Note: '()' correspond to the letters used in the product bulletin

Click here for the 3D model.

Dimensions		
Chip Size	6560	
L	16.5mm +/-0.2mm	
W	15mm +/-0.2mm	
Т	7mm +/-0.2mm	
F	0.5mm NOM	
De alsonium Conneiliantium		

Packaging Specifications	
Packaging	T&R
Packaging Quantity	500

Specifications	
Capacitance	0.068 uF
Tolerance	10%
Voltage DC	1000 VDC
Voltage AC	350 VAC
Temperature Range	-55/+125°C
Rated Temperature	100°C
Dissipation Factor	0.6% 1kHz, 1% 10kHz, 2% 100kHz
Insulation Resistance	30 GOhms
Max dV/dt	600 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/28/2025 © 2006 - 2025 YAGEO