

PHE426HB6330JR06

Aliases (F426BG334J250C, PHE426HB6330JB15R06)

Not for New Design

PHE426/F426, Film, Metallized Polypropylene, General Purpose, 0.33 uF, 5%, 250 VDC, 85°C, 15mm



Click [here](#) for the 3D model.

Dimensions

L	18mm MAX
H	12mm MAX
T	6mm MAX
S	15mm +/-0.4mm
LL	6mm NOM
F	0.8mm NOM

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	1000

General Information

Series	PHE426/F426
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	1.697 g
Notes	Series Replaced by R75.

Specifications

Capacitance	0.33 uF
Capacitance Tolerance	5%
Voltage DC	250 VDC, 185 VDC (105C)
Voltage AC	160 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 1kHz, 0.1% 10kHz
Insulation Resistance	100 GOhms
Max dV/dt	120 V/us
Inductance	6 nH