



Click [here](#) for the 3D model.

Dimensions

L	18mm -0.5mm
H	15mm -0.5mm
T	8mm -0.5mm
S	15mm +/-0.4mm
LL	17mm -1mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	400

General Information

Series	PHE429/F429
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Miscellaneous	The Rated Voltage Decreases 1.3%/C Between +85C And +110C. Rthha= 71 C/W (85C), 0.2 m/s.

Specifications

Capacitance	0.47 uF
Capacitance Tolerance	10%
Voltage DC	420 VDC, 338 VDC (105C)
Voltage AC	220 VAC
Temperature Range	-55/+110°C
Rated Temperature	85°C
Dissipation Factor	0.1% 1kHz
Insulation Resistance	63.8298 GOhms
Max dV/dt	150 V/us
Inductance	6 nH