

## F464BY223J2K5L

Obsolete

F464, Film, Metallized Polypropylene, General Purpose, 0.022 uF, 5%, 2,500 VDC, 85°C, 15 mm



Click [here](#) for the 3D model.

### General Information

|                          |   |
|--------------------------|---|
| Series                   | F464  |
| Dielectric               | Metallized Polypropylene  |
| Style                    | Radial  |
| Features                 | MKP Pulse   |
| RoHS                     | Yes   |
| Termination              | Tinned Wire   |
| Lead                     | Wire Leads  |
| AEC-Q200                 | No  |
| Typical Component Weight | 6.157 g   |
| Miscellaneous            | The Rated Voltage Decreases 2%/C Between +85C And +105C (1.25%/C For AC). ClimCat: 55/105/56. |
| Notes                    | Series Replaced by R75.   |

### Specifications

|                       |                                       |
|-----------------------|---------------------------------------|
| Capacitance           | 0.022 uF                              |
| Tolerance             | 5%                                    |
| Voltage DC            | 2500 VDC, 1500 VDC (105C)             |
| Voltage AC            | 900 VAC                               |
| Temperature Range     | -55/ +105°C                           |
| Rated Temperature     | 85°C                                  |
| Dissipation Factor    | 0.04% 1kHz, 0.06% 10kHz, 0.25% 100kHz |
| Insulation Resistance | 100 GOhms                             |
| Max dV/dt             | 4,500 V/us                            |

### Dimensions

|    |                  |
|----|------------------|
| L  | 18mm -0.5mm      |
| H  | 19mm -0.5mm      |
| T  | 11mm -0.5mm      |
| S  | 15mm +0.6/-0.1mm |
| H0 | 18.5mm +/-0.5mm  |
| F  | 0.8mm +/-0.05mm  |
| G  | 0.5mm NOM        |

### Packaging Specifications

|                    |     |
|--------------------|-----|
| Packaging          | T&R |
| Packaging Quantity | 250 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.