


PHE426HD7100JR06L2

Aliases (F426DF105J250C, PHE426HD7100JD17R06L2)

Not for New Design

PHE426/F426, Film, Metallized Polypropylene, General Purpose, 1 uF, 5%, 250 VDC, 85°C, 22.5mm



Click [here](#) for the 3D model.

Dimensions

L	26mm MAX
H	16.5mm MAX
T	7mm MAX
S	22.5mm +/- 0.4mm
LL	6mm NOM
F	0.8mm NOM

Packaging Specifications

Packaging	Tray
Packaging Quantity	216

General Information

Series	PHE426/F426
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	3.867 g
Notes	Series Replaced by R75.

Specifications

Capacitance	1 uF
Capacitance Tolerance	5%
Voltage DC	250 VDC, 185 VDC (105C)
Voltage AC	160 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.1% 1kHz, 0.1% 10kHz
Insulation Resistance	30 GOhms
Max dV/dt	80 V/us
Inductance	6 nH