

MMK37.5106K400R06L4TRAY

Aliases (F601RP106K400C, MMK37,5106K400R06L4TRAY)

Not for New Design • Recommended Replacement Series R60

MMK/F601, Film, Metallized Polyester, General Purpose, 10 uF, 10%, 400 VDC, 85°C, 37.5mm



Click [here](#) for the 3D model.

Dimensions

L	41mm MAX
H	38mm MAX
T	21mm MAX
S	37.5mm +/-0.5mm
LL	5mm NOM
F	1mm NOM

Packaging Specifications

Packaging	Tray
Packaging Quantity	84

General Information

Series	MMK/F601
Dielectric	Metallized Polyester
Style	Radial
Features	DC Multipurpose Applications
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	34.4 g
Notes	Not for new design - the replacement series is: R60.

Specifications

Capacitance	10 uF
Capacitance Tolerance	10%
Voltage AC	200 VAC
Voltage DC	400 VDC, 310 VDC (100C)
Temperature Range	-55/+100°C
Rated Temperature	85°C
Dissipation Factor	1% 1kHz
Insulation Resistance	1 GOhms
Max dV/dt	5 V/us
Inductance	6 nH