



Click [here](#) for the 3D model.

#### Dimensions

L	7.2mm -0.5mm
H	6.5mm -0.5mm
T	2.5mm -0.5mm
S	5mm +/-0.4mm
LL	20mm +5mm
F	0.5mm +/-0.05mm
G	0.5mm NOM

#### Packaging Specifications

Packaging	Bulk
Packaging Quantity	4000

#### General Information

Series	F612
Dielectric	Metallized Polyester Stacked
Style	Radial
Features	MKT (Stacked), DC Multipurpose Applications
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Miscellaneous	The Rated Voltage Decreases 1.25%/C Between +85C And +105C (For +125C, Please Consult KEMET). This 5% tolerance part is available on request. ClimCat: 55/105/56.

#### Specifications

Capacitance	0.022 uF
Capacitance Tolerance	5%
Voltage DC	250 VDC, 187.5 VDC (105C)
Voltage AC	140 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.8% 1kHz, 1.2% 10kHz, 2.5% 100kHz
Insulation Resistance	30 GOhms
Max dV/dt	130 V/us
Inductance	6 nH