

PHE845VF6100MR06L2

Aliases (F845FE104M760C, PHE845VF6100MF11R06L2)

PHE845/F845, Film, Metallized Polypropylene, Safety, 0.1 uF, 20%, 1500 VDC, 760 VAC (X1), 105°C, 27.5mm



Click [here](#) for the 3D model.

Dimensions	
L	31.5mm MAX
H	20.5mm MAX
T	10.5mm MAX
S	27.5mm +/-0.4mm
LL	6mm -1mm
F	0.8mm NOM

Packaging Specifications	
Packaging	Tray
Packaging Quantity	216

General Information	
Series	PHE845/F845
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Safety Class	X1
Qualifications	ENEC, UL, cUL
AEC-Q200	No
THB Performance	Yes
Typical Component Weight	7.2 g

Specifications	
Capacitance	0.1 uF
Capacitance Tolerance	20%
Voltage DC	1500 VDC
Voltage AC	760 VAC (X1)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Dissipation Factor	0.1% 1kHz, 0.2% 10kHz, 0.6% 100kHz
Insulation Resistance	30 GOhms
Max dV/dt	100 V/us