




F862, Film, Metallized Polypropylene, Automotive Safety, 1 uF, 10%, 630 VDC, 310 VAC (X2), 110°C, 27.5 mm



Click	here	for	the	3D	model
CIICK	חבו כ	101	uic	$^{\circ}$	HOUGE

General Information		
Series	F862	
Dielectric	Metallized Polypropylene	
Style	Radial	
Features	MKP EMI, Aumotive Grade, Harsh Environmental Conditions, Heavy Duty	
RoHS	Yes	
Termination	Cut (Tinned Wire)	
Lead	Cut/Short	
Safety Class	X2	
Qualifications	ENEC, UL, cUL, CQC, AEC- Q200	
AEC-Q200	Yes	
THB Performance	Yes	
Typical Component Weight	9.133 g	
Miscellaneous	ClimCat: 40/110/56/B.	
Shelf Life	104 Weeks	

Dimensions	
L	31.5mm -0.7mm
Н	20mm -0.7mm
Т	11mm -0.7mm
S	27.5mm +/-0.4mm
LL	4mm +2mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications		
Packaging	Pizza, Box	
Packaging Quantity	300	

Specifications	
Capacitance	1uF
Tolerance	10%
Voltage DC	630 VDC
Voltage AC	310 VAC (X2)
Temperature Range	-40/+110°C
Rated Temperature	110°C
Dissipation Factor	0.2% 1kHz
Insulation Resistance	10 GOhms
Max dV/dt	150 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/06/2025 © 2006 - 2025 YAGEO