



Click [here](#) for the 3D model.

#### Dimensions

L	7.2mm -0.5mm
H	10mm -0.5mm
T	5mm -0.5mm
S	5mm +/-0.4mm
LL	20mm +5mm
F	0.6mm +/-0.05mm
G	0.5mm NOM

#### Packaging Specifications

Packaging	Bulk
Packaging Quantity	1500

#### General Information

Series	F622
Dielectric	Metallized Polyester Stacked
Style	Radial
Features	MKT (Stacked), DC Multipurpose Applications
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Miscellaneous	The Rated Voltage Decreases 1.25%/C Between +85C And +125C. ClimCat: 55/125/56.

#### Specifications

Capacitance	0.22 uF
Capacitance Tolerance	10%
Voltage DC	100 VDC, 50 VDC (125C)
Voltage AC	63 VAC
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	0.8% 1kHz, 1.2% 10kHz
Insulation Resistance	15 GOhms
Max dV/dt	300 V/us
Inductance	6 nH